

NOMENCLATURE:

| Model | <u>DF</u> | <u>S</u> | <u>80</u> | <u>15</u> | <u>05</u> | <u>H</u> |
|-------|-----------|----------|-----------|-----------|-----------|----------|
| | 1 | 2 | 3 | 4 | 5 | 6 |

1. Series Name: DF = DC Fan
2. Bearing Type: S = Sleeve
C = One Ball and One Sleeve
B = Ball
3. Frame Size: 80 = 80 mm Long By 80 mm Wide
4. Frame Height: 15 = 15.4 mm
5. Voltage: 05 = 5 V dc
6. Speed: H = High Speed
M = Medium speed
L = Low Speed



Product Service

CERTIFICATE**No. B 08 07 34564 016****Model(s):**

DFx801505y series

Difference

DF x 8015 05 y

1 2 3 4 5

1 = Commercial Code

D: DC

F: FAN

2 = Bearing type

"x" can be C, B or S

"C" : 1 Ball + 1 Sleeve

"B" : 2 Ball

"S" : Sleeve or equal

3 = Frame size by Fan thick

"8015" : 80 x 80 x 15 mm

4 = Input Voltage

"05" : 5 Vdc

5 = Fan speed

"y" can be H, M or L

"H" : High speed

"M" : Medium speed

"L" : Low speed

Parameters:

Rated input voltage:

5 Vdc

Rated input power:

See attachment

Protection class:

III

Max. ambient temperature:

40°C

Degree of protection

against ingress of liquids:

Ordinary

Remark: When installing, all requirements of below mentioned test standards must be fulfilled.

**Tested
according to:**

EN 60950-1/A11:2004

**Production
Facility(ies):**

52640

Page 2 of 3



2 EUT DESCRIPTION

| | |
|---------------------|--|
| Product | DC Fans |
| Trade Name | YLTC |
| Model | DFS4020; DFB4020; DFB4028; DFS4510; DFB4510; DBS5512; DBC5512; DBB5512; DFS6010; DFC6010; DFB6010; DFS6020; DFB6020; DFC6020; DFS7010; DFC7010; DFS8010; DFC8010; DFS8015; DFC8015; DFB8015; DFC8020; DFB8020; DFS8020; DBB9733; DFS1225; DFB1225; DFB1232; DFS1238; DFB1238; DFS9238; DFB9238; DFS4910; DFC4910; DFB4910; DFS6025; DFB6025; DFC6025; DFS4507; DFB4507 |
| Housing Type | N/A |
| EUT Power Rating | See as below |
| DC Power Cable Type | Unshielded, 0.2m |

Note:

1. Difference between of forty model numbers (list on this report) are list as below:

| Model | Volts | Speed | Model | Volts | Speed |
|---------|---------|-------|---------|----------|-------|
| DFS4020 | 5/12/24 | H/M/L | DFB8015 | 5/12/24 | H/M/L |
| DFB4020 | 5/12/24 | H/M/L | DFC8020 | 12/24 | H/M/L |
| DFB4028 | 5/12/24 | H/M/L | DFB8020 | 12/24 | H/M/L |
| DFS4510 | 12 | H/M/L | DFS8020 | 12/24 | H/M/L |
| DFB4510 | 12 | H/M/L | DBB9733 | 12 | H/M/L |
| DBS5512 | 5 | H | DFS1225 | 12/24 | H/M/L |
| DBC5512 | 5 | H | DFB1225 | 12/24 | H/M/L |
| DBB5512 | 5 | H | DFB1232 | 12/24 | H/M/L |
| DFS6010 | 12 | H/M/L | DFS1238 | 12/24/48 | H/M/L |
| DFC6010 | 12 | H/M/L | DFB1238 | 12/24/48 | H/M/L |
| DFB6010 | 12 | H/M/L | DFS9238 | 12/24 | H/M/L |
| DFS6020 | 12 | H/M/L | DFB9238 | 12/24 | H/M/L |
| DFB6020 | 12 | H/M/L | DFS4910 | 12 | H/M/L |
| DFC6020 | 12 | H/M/L | DFC4910 | 12 | H/M/L |
| DFS7010 | 12/24 | H/M/L | DFB4910 | 12 | H/M/L |
| DFC7010 | 12/24 | H/M/L | DFS6025 | 24 | H/M/L |
| DFS8010 | 12/24 | H/M/L | DFB6025 | 24 | H/M/L |
| DFC8010 | 12/24 | H/M/L | DFC6025 | 24 | H/M/L |
| DFS8015 | 5/12 | H/M/L | DFS4507 | 5/12 | H/M |
| DFC8015 | 5/12/24 | H/M/L | DFB4507 | 5/12 | H/M |

2. Client consigns only one sample (model number is DFS1238) to test. Therefore, testing Lab. just guarantees the units, which have been tested.